



### Metric table

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>		d <sub>3</sub>	b	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	t		
	GB	GB-FP						GB	GB-FP	
34 1.34	M 6	M 8	-	7 0.28	14 0.55	18 0.71	4 0.16	.3 .01	9 0.35	15 0.59
47 1.85	M 6	M 8	M 8	9 0.35	17 0.67	20 0.79	4 0.16	.3 .01	13 0.51	15 0.59

### Specification

- Wing body  
Nylon plastic  
- Glass filled  
- Temperature resistant up to 230 °F (110 °C)  
- Black, matte finish
- Tapped insert  
Brass
- [Plastic Characteristics](#) → page 2135
- [RoHS compliant](#)

### On request

- For certain minimum quantities, custom colors or special studs

### Information

GB and GB-FP wing nuts offer an extended hub for better surface contact and a comfortable grip for quick two finger clamping applications.

The tapped through type allows full clamping, unrestricted the threaded stud the wing nut is being used on.

see also...

- [Wing Screws GP \(with Steel Threaded Stud\)](#) → page 671

How to order (Blind tapped insert) 1 2 <b>GB-34-M6</b>	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
How to order (Through tapped insert) 1 2 <b>GB-FP-47-M8</b>	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>