



Inch table

1 For thread size	2 d ₁	b	s
1/4	1.25 31.8	0.28 7.1	0.25 6.4
5/16	1.25 31.8	0.34 8.6	0.31 7.9
3/8	1.50 38.1	0.41 10.4	0.38 9.7
1/2	2.00 50.8	0.53 13.5	0.38 9.7
5/8	2.13 54.1	0.63 16.0	0.38 9.7
3/4	2.50 63.5	0.78 19.8	0.44 11.2
7/8	2.63 66.8	0.91 23.1	0.50 12.7
1.00	3.00 76.2	1.03 26.2	0.56 14.2

Dimensions in: inches - millimeters

Specification

- Cold finished steel
- Case-hardened
- Black oxide finish
- All sharp edges removed
- Surface flat and parallel

• RoHS compliant

3

ST

Information

HDCW heavy duty C-washers are designed to be slid in and out of position on a bolt or shaft in a partially completed assembly or fixture. They can also be used as a retention device to keep components in place.

see also...

- Knurled C-Washers GN 183 (Metric Size) → page QVX
- Swing C-Washers SCW → page QVX

<p>How to order</p> <p>1 2 3</p> <p>HDCW-1/4-1.25-ST</p>	1 For thread size
	2 Outer diameter d ₁
	3 Material