



- 2 Type**
- A Without screw / tapped insert
 - B With hex tapped insert

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ Thread	d ₃	d ₄	h ₁	h ₂	A/F	t ₁	t ₂	t ₃ min.
11* 0.43	M 4	5.5 0.22	8.2 0.32	6.5 0.26	-	-	1 0.04	4 0.16	-
12 0.47	M 5	7 0.28	9.3 0.37	8 0.31	11 0.43	10 0.39	1.5 0.06	5.3 0.21	6 0.24
15 0.59	M 6	8.5 0.33	11.5 0.45	10 0.39	14 0.55	12 0.47	2 0.08	6 0.24	7 0.28
19 0.75	M 8	11 0.43	15 0.59	13 0.51	18 0.71	16 0.63	2 0.08	7.5 0.30	8.5 0.33
24 0.94	M 10	13 0.51	20 0.79	16 0.63	23.5 0.93	21 0.83	2.2 0.09	9.2 0.36	10 0.39
26 1.02	M 12	16 0.63	22 0.87	19 0.75	26 1.02	22 0.87	2.5 0.10	10.5 0.41	12 0.47

* This size is only available in type A

Specification

- Protective cap
Rubber CR (Neoprene®)
- 85±5 shore A
- Black
- Hex tapped insert
Steel, zinc plated, blue passivated finish
- *Elastomer Characteristics* → page 2135
- RoHS compliant

Information

GN 806 protective caps can be used with ISO 4017 (DIN 933) hex head screws or with threaded pins (type B) as thrust pins with soft clamping surface, or as soft end stop bolts. The tapped insert version allows for expanded applications requiring, for example, extra long threaded pins.

A typical application is their use in conjunction with toggle clamps as stopper bolts or clamping pads.

see also...

- *Vibration / Shock Absorption Mounts GN 352 / GN 452 (Cylindrical Type)* → page 1620
- *Vibration / Shock Absorption Mounts GN 353 / GN 453 (Conical Type)* → page 1624

<p>How to order</p> <p>GN 806-24-B</p>	1	Outer diameter d ₁
	2	Type