


Metric



Metric table

Dimensions in: millimeters / inches

d₁	d₂		d₃	l₁	l₂
17 0.67	M 6	M 8	12 0.47	45 1.77	8 0.31
21 0.83	M 8	M 10	16 0.63	56 2.20	10 0.39
23 0.91	M 8	M 10	16 0.63	61 2.40	10 0.39
25 0.98	M 8	M 10	18 0.71	71 2.80	13 0.51
28 1.10	M 10	M 12	20 0.79	92 3.62	13 0.51
29 1.14	M 10	M 12	20 0.79	122 4.80	13 0.51

Specification

Handle

Plastic, Phenolic (PF)

- Operating temperature up to 266 °F (130 °C)
- Black, shiny finish

Threaded spindle

Steel

- Zinc plated
- With wrench flats

RoHS

MCG cylindrical revolving handles can be used on most any device where a leverage for turning is required, i.e. handwheels or crank handles.

see also...

	Page
MGR Retractable Handles (Phenolic Plastic)	QVX
PGR Retractable Handles (Nylon Plastic)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order

MCG-17-M6

- | | |
|---|-----------------------|
| 1 | Handle diameter d_1 |
| 2 | Thread d_2 |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

