



Universal table

Dimensions in: millimeters - inches

¹ l ₁	² d ₁ Pilot hole	l ₂	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄	d ₅ Ø Handle	d ₆
65 2.56	P 4	87 3.43	18 0.71	16 0.63	27 1.06	33 1.30	30 1.18	10 0.39	50 1.97	21 0.83	M 6
80 3.15	P 4	105 4.13	22 0.87	19 0.75	30 1.18	36 1.42	32 1.26	10 0.39	50 1.97	21 0.83	M 6
100 3.94	P 4	128 5.04	24 0.94	22 0.87	34 1.34	40 1.57	37 1.46	10 0.39	70 2.76	23 0.91	M 8
130 5.12	P 6	162 6.38	28 1.10	25 0.98	40 1.57	49 1.93	44 1.73	14 0.55	90 3.54	26 1.02	M 8
160 6.30	P 6	196 7.72	34 1.34	28 1.10	45 1.77	55 2.17	49 1.93	15 0.59	90 3.54	26 1.02	M 10

Specification

- Crank body
Nylon plastic
- Glass fiber reinforced
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish
- Hub bushing
Steel, zinc plated
- Revolving handle
Nylon plastic
- Black, matte finish
- Threaded spindle
Steel, zinc plated
- Keyways *WN / DIN 6885* → page XYZ / XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Other modifications such as inch and metric bores, squares, keyways, set screw holes, etc.

Information

MH-MEP crank handles are of modern design and are suitable for light duty applications.

see also...

- Crank Handles MV-M → page 284
- Crank Handles MH-PGR → www.jwwinco.com
- Crank Handles MH-MRS → www.jwwinco.com

How to order MH-MEP-65-P4	¹ Length l ₁
	² Pilot hole d ₁