



SS Stainless Steel

4 Type

- B** Non lock-out, without lock nut
- BK** Non lock-out, with lock nut
- C** Lock-out, without lock nut
- CK** Lock-out, with lock nut
- G** With threaded stem, without lock nut
- GK** With threaded stem, with lock nut

Specification

- Threaded body
 - Steel, blackened finish —
 - Stainless steel AISI 303 **NI**
 - Plunger pin hardened
 - Plunger pin chemically nickel plated (only available in metric sizes)
- Knob
 - Plastic
 - Technopolymer (Polyamide PA)
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish —
 - Red, RAL 3000, matte finish **RT**
 - Not removable
- Inch size lock nut
 - Steel, blackened finish
 - ANSI/ASME B18.2.2
- Metric size lock nut
 - Steel, blackened finish
 - DIN 439 B / ISO 8675
 - Stainless steel (A2)
 - DIN 439 B / ISO 8675
- [Load Rating Information → page 2103](#)
- [ISO Fundamental Tolerances → page 2129](#)
- [Plastic Characteristics → page 2135](#)
- [Stainless Steel Characteristics → page 2143](#)
- [RoHS compliant](#)

Information

GN 817 indexing plungers with lock-out (Type C / CK) are used for applications where the plunger pin needs to stay in its retracted position. To achieve this, the knob is rotated by 90 degrees after being retracted. A notch keeps the plunger in the retracted position.

This indexing plunger has the unique feature of the pull knob partially enclosing the top of the plunger body, allowing less debris to enter into the mechanism.

Type G and GK with threaded stem are for applications where a special knob or attachment is required, or for such cases where the spindle is linked directly to an operating mechanism.

see also...

- [List of Indexing Plunger Types → page 915](#)

How to order (Inch, steel, black knob)	1 Pin diameter d_1
1 2 3 4	2 Stroke l_1
GN817-4-6-5/16X18-C	3 Thread d_2
	4 Type

How to order (Metric, stainless steel, red knob)	1 Pin diameter d_1
1 2 3 4 5 6	2 Stroke l_1
GN817-10-12-M16X1.5-BK-NI-RT	3 Thread d_2
	4 Type
	5 Material
	6 Color

Inch table

Dimensions in: inches - millimeters

1 d ₁ Pin ^{-0.001} / _{-0.002} Bore +0.001	2 l ₁	3 d ₂	d ₃	d ₄	d ₅	k	l ₂	l ₃	l ₄	l ₅	l ₆	A/F	Spring load ≈	
													Initial	End
0.16 4	0.16 4	5/16 x 18	0.63 16	M 3	0.28 7	0.55 14	1.38 35	0.63 16	0.20 5	0.18 4.5	0.10 2.5	0.39 10	1.01 lbf 4.5 N	2.70 lbf 12 N
0.16 4	0.24 6	5/16 x 18	0.63 16	M 3	0.28 7	0.55 14	1.38 35	0.63 16	0.20 5	0.18 4.5	0.10 2.5	0.39 10	0.90 lbf 4 N	2.81 lbf 12.5 N
0.20 5	0.20 5	3/8 x 16	0.75 19	M 4	0.31 8	0.63 16	1.57 40	0.71 18	0.24 6	0.22 5.5	0.12 3	0.47 12	1.12 lbf 5 N	3.37 lbf 15 N
0.20 5	0.31 8	3/8 x 16	0.75 19	M 4	0.31 8	0.63 16	1.57 40	0.71 18	0.24 6	0.22 5.5	0.12 3	0.47 12	1.12 lbf 5 N	4.05 lbf 18 N
0.24 6	0.24 6	1/2 x 13	0.91 23	M 5	0.35 9	0.79 20	1.89 48	0.87 22	0.24 6	0.28 7	0.14 3.5	0.55 14	1.46 lbf 6.5 N	4.27 lbf 19 N
0.24 6	0.35 9	1/2 x 13	0.91 23	M 5	0.35 9	0.79 20	1.89 48	0.87 22	0.24 6	0.28 7	0.14 3.5	0.55 14	1.35 lbf 6 N	5.62 lbf 25 N
0.31 8	0.31 8	5/8 x 11	1.10 28	M 6	0.39 10	0.94 24	2.28 58	1.02 26	0.31 8	0.33 8.5	0.16 4	0.67 17	1.91 lbf 8.5 N	5.85 lbf 26 N
0.31 8	0.47 12	5/8 x 11	1.10 28	M 6	0.39 10	0.94 24	2.28 58	1.02 26	0.31 8	0.33 8.5	0.16 4	0.67 17	1.91 lbf 8.5 N	6.29 lbf 28 N
0.39 10	0.47 12	5/8 x 11	1.10 28	M 6	0.39 10	0.94 24	2.28 58	1.02 26	0.31 8	0.33 8.5	0.16 4	0.67 17	2.14 lbf 9.5 N	8.54 lbf 38 N
0.47 12	0.59 15	3/4 x 16	1.30 33	M 6	0.47 12	1.12 28.5	2.81 71.5	1.30 33	0.39 10	0.33 8.5	0.16 4	0.87 22	2.59 lbf 11.5 N	8.99 lbf 40 N
0.63 16	0.79 20	1 x 8	1.30 33	M 8	0.59 15	1.12 28.5	3.09 78.5	1.50 38	0.47 12	0.45 11.5	0.20 5	1.06 27	2.92 lbf 13 N	12.14 lbf 54 N

Metric table

Dimensions in: millimeters - inches

1 d ₁ Pin ^{-0.02} / _{-0.05} Bore H7	2 l ₁	3 d ₂	d ₃	d ₄	d ₅	k	l ₂	l ₃	l ₄	l ₅	l ₆	A/F	Spring load ≈	
													Initial	End
4 0.16	4 0.16	M 8 x 1	16 0.63	M 3	7 0.28	14 0.55	35 1.38	16 0.63	5 0.20	4.5 0.18	2.5 0.10	10 0.39	4.5 N 1.01 lbf	12 N 2.70 lbf
4 0.16	6 0.24	M 8 x 1	16 0.63	M 3	7 0.28	14 0.55	35 1.38	16 0.63	5 0.20	4.5 0.18	2.5 0.10	10 0.39	4 N 0.90 lbf	12.5 N 2.81 lbf
5 0.20	5 0.20	M 10 x 1	19 0.75	M 4	8 0.31	16 0.63	40 1.57	18 0.71	6 0.24	5.5 0.22	3 0.12	12 0.47	5 N 1.12 lbf	15 N 3.37 lbf
5 0.20	8 0.31	M 10 x 1	19 0.75	M 4	8 0.31	16 0.63	40 1.57	18 0.71	6 0.24	5.5 0.22	3 0.12	12 0.47	5 N 1.12 lbf	18 N 4.05 lbf
6 0.24	6 0.24	M 12 x 1.5	23 0.91	M 5	9 0.35	20 0.79	48 1.89	22 0.87	6 0.24	7 0.28	3.5 0.14	14 0.55	6.5 N 1.46 lbf	19 N 4.27 lbf
6 0.24	9 0.35	M 12 x 1.5	23 0.91	M 5	9 0.35	20 0.79	48 1.89	22 0.87	6 0.24	7 0.28	3.5 0.14	14 0.55	6 N 1.35 lbf	25 N 5.62 lbf
8 0.31	8 0.31	M 16 x 1.5	28 1.10	M 6	10 0.39	24 0.94	58 2.28	26 1.02	8 0.31	8.5 0.33	4 0.16	17 0.67	8.5 N 1.91 lbf	26 N 5.85 lbf
8 0.31	12 0.47	M 16 x 1.5	28 1.10	M 6	10 0.39	24 0.94	58 2.28	26 1.02	8 0.31	8.5 0.33	4 0.16	17 0.67	8.5 N 1.91 lbf	28 N 6.29 lbf
10 0.39	12 0.47	M 16 x 1.5	28 1.10	M 6	10 0.39	24 0.94	58 2.28	26 1.02	8 0.31	8.5 0.33	4 0.16	17 0.67	9.5 N 2.14 lbf	38 N 8.54 lbf
12 0.47	15 0.59	M 20 x 1.5	33 1.30	M 6	12 0.47	28.5 1.12	71.5 2.81	33 1.30	10 0.39	8.5 0.33	4 0.16	22 0.87	11.5 N 2.59 lbf	40 N 8.99 lbf
16 0.63	20 0.79	M 24 x 2	33 1.30	M 8	15 0.59	28.5 1.12	78.5 3.09	38 1.50	12 0.47	11.5 0.45	5 0.20	27 1.06	13 N 2.92 lbf	54 N 12.14 lbf

