



Metric



Metric table

Dimensions in: millimeters / inches

d ₁	d ₂	d ₃	d ₄	d ₅	l ₁	l ₂	l ₃	l ₄	l ₅	l ₆	l ₇	l ₈
21 0.83	M 5	17 0.67	7 0.28	2.5 0.10	57 2.24	7 0.28	8 0.31	54.5 2.15	16.5 0.65	14 0.55	6.3 0.25	4 0.16
23 0.91	M 6	19 0.75	8 0.31	2.5 0.10	77 3.03	7 0.28	8 0.31	84.5 3.33	17.5 0.69	18 0.71	7.5 0.30	4 0.16
26 1.02	M 6	21 0.83	8 0.31	2.5 0.10	97 3.82	7 0.28	10 0.39	96.5 3.80	19 0.75	20 0.79	7.5 0.30	4 0.16

Specification

Handle

Nylon plastic

- Operating temperature up to 230 °F (110 °C)
- Black, matte finish
- Revolving

Retractable mechanism

Steel, zinc plated

RoHS

On request

- For certain minimum quantities, other handle colors

Suitable for applications in which it is preferred that the revolving handle be folded away when in the rest position, and when a shorter protruding distance of the overall length is required. The handle can be folded in both directions.

see also...

PGR Retractable Handles (Nylon Plastic)

MGR Retractable Handles (Phenolic Plastic)

Page

QVX

QVX

Technical Information

Plastic Characteristics

QVX

How to order

MRS-21-M5

1 Handle diameter d₁

2 Thread d₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

