




Metric table

1										Dimensions in: millimeters / inches	
l ₁	h ₁	h ₂	h ₃	h ₄	l ₂	l ₃	l ₄	m ₁ ±0.1	m ₂		
90 3.54	29 1.14	16.5 0.65	63 2.48	20 0.79	135 5.31	74 2.91	41 1.61	80 3.150	8 0.31		

Specification		2
Handle		
Plastic, Polyamide (PA)		
• Glass fiber reinforced		
• Operating temperature		
-22 °F to +212 °F (-30 °C to +100 °C)		
• Color		
- Black, RAL 9005, matte finish	● SW	
- Gray, RAL 7035, matte finish	● GR	
- White, RAL 9002, matte finish	○ WS	
Pin		
Stainless steel AISI 303		
Return springs		
Stainless steel AISI 302		

RoHS	
On request	
Various metric size fasteners and kit packaging	

Folding handles EN 825.1 are used in applications where the handle must not protrude. After releasing the handle, it returns to its starting position by spring-loaded return.

see also...	Page
GN 425.2 Folding Handles (Steel / Stainless Steel, Retained in Both End Positions)	QVX
GN 425.5 Folding Handles (Steel / Stainless Steel, Retained in Both End Positions)	QVX
EN 825.2 Folding Handles with Recessed Tray (Plastic, with Spring-Loaded Return)	QVX

Technical Information	
Strength Values	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX