



**Metric table**

Dimensions in: millimeters - inches

d	l <sub>1</sub>		Metric bolt size	Inch bolt size	b <sub>1</sub>	b <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>	l <sub>3</sub>
9 .35	100 3.94	-	M 8	5/16	30 1.18	16 .63	15 .59	3.8 .15	32 1.26	18 .71
11 .43	125 4.92	-	M 10	3/8	30 1.18	20 .79	20 .79	5 .20	38 1.50	24 .94
14 .55	160 6.30	-	M 12	1/2	40 1.57	24 .94	25 .98	6.3 .25	47 1.85	30 1.18
14 .55	200 7.87	-	M 12	1/2	40 1.57	24 .94	25 .98	6.3 .25	47 1.85	30 1.18
18 .71	200 7.87	250 9.84	M 16	5/8	50 1.97	28 1.10	30 1.18	7.5 .30	57 2.24	36 1.42
22 .87	250 9.84	315 12.40	M 20	3/4	60 2.36	35 1.38	40 1.57	10 .39	68 2.68	45 1.77
26 1.02	250 9.84	315 12.40	M 24	1	70 2.76	43 1.69	40 1.57	10 .39	83 3.27	56 2.20
34 1.34	315 12.40	400 15.75	M 30	1 1/4	80 3.15	50 1.97	50 1.97	12.5 .49	88 3.46	56 2.20

**Specification**

- Forked clamp  
Tempered steel, lacquer painted finish
- RoHS compliant

**Accessory**

- DIN 787 T-slot bolt → page QVX
- DIN 6330 fixture nut → page QVX
- DIN 6340 heavy duty flat washer → page QVX
- DIN 508 T-slot nut → page QVX
- DIN 6379 double-ended threaded stud → page QVX

**Information**

No. 6315 GN fork clamps with shoe end and open slot, have a large offering of clamp size options. They range from 3.94" (100 mm) to 15.75" (400 mm) in length with the ability to clamp small to very large parts.

see also...

- Forked Clamps DIN 6315C → page QVX
- Tapered Fork Clamps DIN 6315B → page QVX

<p>How to order</p> <p><b>NO.6315GN-22-250</b></p>	1	Diameter d
	2	Length l <sub>1</sub>