



SS Stainless Steel

3 Type

- D** With tapped through bore
- E** With tapped blind bore

Inch table

Dimensions in: inches - *millimeters*

1 d_1	2 d_2	d_3	d_4	b	h_1	h_2	t_1 min.	t_2
1.81 46	1/4 x 20	0.51 13	0.26 6.5	0.24 6	0.89 22.5	0.24 6	0.47 12	0.39 10
1.81 46	5/16 x 18	0.51 13	0.33 8.5	0.24 6	0.89 22.5	0.24 6	0.59 15	0.51 13
2.28 58	5/16 x 18	0.63 16	0.33 8.5	0.28 7	1.04 26.5	0.28 7	0.59 15	0.51 13
2.28 58	3/8 x 16	0.63 16	0.41 10.5	0.28 7	1.04 26.5	0.28 7	0.71 18	0.63 16

Metric table

Dimensions in: millimeters - *inches*

1 d_1	2 d_2	d_3	d_4	b	h_1	h_2	t_1 min.	t_2
46 1.81	M 6	13 0.51	6.5 0.26	6 0.24	22.5 0.89	6 0.24	12 0.47	10 0.39
46 1.81	M 8	13 0.51	8.5 0.33	6 0.24	22.5 0.89	6 0.24	15 0.59	13 0.51
58 2.28	M 8	16 0.63	8.5 0.33	7 0.28	26.5 1.04	7 0.28	15 0.59	13 0.51
58 2.28	M 10	16 0.63	10.5 0.41	7 0.28	26.5 1.04	7 0.28	18 0.71	16 0.63

Specification

4

- Stainless steel precision casting AISI CF-8 Matte shot-blasted finish **MT**
- Stainless Steel Characteristics → page 2143
- RoHS compliant

On request

- Any quantity of the blank version can be tapped or reamed in either inch or metric sizes

Information

The ridges on the wings of GN 834 wing nuts permit a better grip.

see also...

- Wing Nuts GN 432 (Stainless Steel) → page 679
- Wing Nuts GN 434 (Stainless Steel) → page 678
- Three-Lobed Knobs GN 5345 (Stainless Steel) → page 640
- Hand Knobs DIN 6335 (Stainless Steel) → page 626

How to order (Inch)	1 Handle diameter d_1
1 2 3 4	2 Thread d_2
GN 834-58-3/8X16-E-MT	3 Type
	4 Finish
How to order (Metric)	1 Handle diameter d_1
1 2 3 4	2 Thread d_2
GN 834-46-M8-D-MT	3 Type
	4 Finish