



Mounting example



Metric table

Dimensions in: millimeters - inches

b Size of the slide	l₁	d For socket cap screws DIN 912	h₁	h₂	l₂	l₃	l₄	l₅
30 1.18	41 1.61	M 2.5	8.4 0.33	4.2 0.17	35.4 1.39	41 1.61	35.4 1.39	6.5 0.26
50 1.97	67 2.64	M 3	14 0.55	7 0.28	58 2.28	67 2.64	58 2.28	10 0.39
80 3.15	105 4.13	M 4	25 0.98	12.5 0.49	92 3.62	105 4.13	92 3.62	14.5 0.57
120 4.72	145 5.71	M 5	27.6 1.09	13.8 0.54	131.8 5.19	145 5.71	131.8 5.19	14.5 0.57

Specification

- Body
Aluminum
Anodized, natural color
- Socket cap screws DIN 912
Stainless steel
- RoHS compliant

Information

With GN 900.2 connecting sets, two GN 900 adjustable slide units can be connected to create an X-Y axis configuration.

The assembly is done via a clamping system that eliminates the use of any kind of mounting holes in the slide. At the same time, the inner slide of the Y-axis can be moved within a limited range.

The small fixing plate serves for the 90° alignment and adjustment of the X-Y axis configuration.

All parts required for mounting are included.

see also...

- Adjustable Slide Units GN 900 → page QVX

<p>How to order</p> <p>GN 900.2-50-67</p>	1	Width b
	2	Length l ₁

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10