


Mounting example



Metric table

Dimensions in: millimeters - inches

¹ b Size of the slide	² l₁	d Socket cap screws DIN 912	h₁	h₂	h₃	l₂	s
30 1.18	41 1.61	M 2.5	18.4 0.72	10 0.39	4.2 0.17	35.4 1.39	6 0.24
50 1.97	67 2.64	M 3	28 1.10	14 0.55	7 0.28	58 2.28	9 0.35
80 3.15	105 4.13	M 4	39 1.54	14 0.55	12.5 0.49	92 3.62	9 0.35
120 4.72	145 5.71	M 5	47.6 1.87	20 0.79	13.8 0.54	131.8 5.19	12 0.47

Specification

- Body
Aluminum
Anodized finish, natural color
- Socket cap screws DIN 912
Stainless steel
- RoHS compliant

Information

GN 900.5 rotary plates allow the adjustable slide units to be positioned at an offset angle to each other. This offers an additional possible axis configuration.

Two plates are connected together in the center so they may be rotated. They are each connected to the adjustable slide units via a clamping system.

All parts required for mounting are included.

see also...

- Adjustable Slide Units GN 900 → page QVX

How to order ¹ ² GN 900.5-80-105	1 Width b
	2 Length l₁

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10