



Universal



3 Type

D With revolving retractable handle

Universal table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Pilot hole	d ₃	d ₄	b	s	l ₁	l ₂	l ₃	l ₄	l ₅	l ₆	d ₅
100 3.94	P 4	24 0.94	21 0.83	20 0.79	15 0.59	24 0.94	12 0.47	46 1.81	52 2.05	98 3.86	50 1.97	M 4
125 4.92	P 6	24 0.94	21 0.83	24 0.94	17 0.67	28 1.10	12 0.47	51 2.01	52 2.05	103 4.06	54 2.13	M 4
160 6.30	P 6	32 1.26	23 0.91	28 1.10	20 0.79	31 1.22	15 0.59	61 2.40	72 2.83	133 5.24	65 2.56	M 5
200 7.87	P 6	40 1.57	26 1.02	32 1.26	24 0.94	40 1.57	15 0.59	74 2.91	92 3.62	166 6.54	79 3.11	M 6

Specification

- Nylon plastic
 - Glass filled
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
- Hub bushing
 - Steel, zinc plated
- Retractable handles PGR → page 52
 - Nylon plastic
 - Black, matte finish
 - Retractable mechanism
 - Chrome plated steel hub
 - Zinc plated steel stem
- Keyways WN / DIN 6885 → page XYZ / XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, cross holes, etc.

Information

SHA-MRP handwheels with revolving retractable handle are distinguished by their modern design. By pulling up on the handle 90°, the handle locks into the rotating position. Disengage the handle by pulling it out and moving it down 90° back to the center of the handwheel. A compression spring secures the handle in either position.

These handwheels are an excellent choice for applications requiring the handle to be kept out of harms way.

see also...

- Solid Disk Handwheels SHA → page 240
- Countersunk Washers GN 184 (for Axial Fixing) → page 1150

How to order

SHA-MRP-160-P6-D

- 1** Handwheel diameter d₁
- 2** Pilot hole d₂
- 3** Type