



**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> A/F	<sup>2</sup> d <sub>2</sub> Thread	<sup>3</sup> l <sub>1</sub>	l <sub>2</sub>	e	Max. load
0.563 14.3	1/4 x 20	1.00 25.4	0.093 2.4	0.625 15.9	1000 lbf 4448.22 N
0.750 19.1	5/16 x 18	1.50 38.1	0.109 2.8	0.842 21.4	2300 lbf 10230.90 N
0.875 22.2	3/8 x 16	1.50 38.1	0.140 3.6	0.986 25.0	3750 lbf 16680.83 N
0.875 22.2	3/8 x 16	2.50 63.5	0.140 3.6	0.986 25.0	3750 lbf 16680.83 N
1.063 27.0	1/2 x 13	2.50 63.5	0.171 4.3	1.204 30.6	5000 lbf 22241.10 N

**Specification**

- Base / stud
- One piece low carbon steel
- - Clear zinc plated
- - No articulation

**Information**

SN 949 hex leveler bolts are ideal for light duty industrial appliances where cost is a primary concern. Common uses are in sheet metal enclosures and appliances.

see also...

- *Willi Glide Leveling Mounts SN 946 (with Plastic / Rubber Pad) → page 1498*
- *Rattle Mounts SN 974 (with Optional Slot) → page 1500*

How to order <sup>1</sup> <sup>2</sup> <sup>3</sup> <b>SN949-0.563-1/4X20-1.00</b>	<b>1</b> Across flats
	<b>2</b> Thread d <sub>2</sub>
	<b>3</b> Length l <sub>1</sub>

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

