



Dimensions in: millimeters - inches

| d ₁ | Rotary range | Concentricity tolerance | Runout tolerance | Max. input torque M _D in Nm | Max. load capacity of the rotary disk | | F max. |
|----------------|--------------|-------------------------|------------------|----------------------------------------|---------------------------------------|------------------------------|--------------------|
| | | | | | Unclamped in Nm | Clamped M _K in Nm | |
| 55 2.17 | 0°... ∞ | ±0.02 ±0.0007 | ±0.02 ±0.0007 | 1.5 | 5 | 10 | 50 N 11.24 lbf |
| 80 3.15 | 0°... ∞ | ±0.03 ±0.0011 | ±0.03 ±0.0011 | 2.5 | 5 | 10 | 100 N 22.48 lbf |