



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> l <sub>1</sub>	<sup>2</sup> d <sub>1</sub>	<sup>3</sup> l <sub>2</sub>						d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub> ≈
45 1.77	M 6	20 0.79	-	-	-	-	-	10 0.39	9 0.35	34 1.34
63 2.48	M 6	20 0.79	-	-	-	-	-	10 0.39	12 0.47	44 1.73
63 2.48	M 8	25 0.98	30 1.18	35 1.38	40 1.57	50 1.97	-	13 0.51	12.5 0.49	42 1.65
78 3.07	M 8	25 0.98	30 1.18	35 1.38	40 1.57	50 1.97	-	13 0.51	15 0.59	52 2.05
78 3.07	M 10	35 1.38	50 1.97	55 2.17	60 2.36	65 2.56	-	16 0.63	16 0.63	50 1.97
92 3.62	M 10	35 1.38	50 1.97	55 2.17	60 2.36	65 2.56	-	16 0.63	16 0.63	60 2.36

**Specification**

- Lever body  
Zinc die-cast  
Powder coated  
Silver, RAL 9006, textured finish ● SR
- Threaded stud / retaining screw  
Stainless steel AISI 303
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**Information**

GN 911 adjustable levers replace the DIN 912 socket cap screws of connector clamps and linear actuator connectors.  
The table of dimensions of the connector clamps and linear actuator connectors shows the matching lever for each screw location.

How to order	<sup>1</sup> Lever length l <sub>1</sub>
	<sup>2</sup> Thread d <sub>1</sub>
	<sup>3</sup> Thread length l <sub>2</sub>
	<sup>4</sup> Color

<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup>  
**GN911-63-M8-30-SR**