



Inch table

Dimensions in: inches - millimeters

¹ d ₁ Outer Ø	² d ₂ Inner Ø	³ d ₃ Thread										
						l ₁	l ₂	t	External diameter of tube	Wall thickness of tube	Comparable material gauge	Load rating
D 1.50	D 1.38	3/8 x 16	1/2 x 13	5/8 x 11	3/4 x 10	1.71 43.4	0.33 8.4	1.00 25.4	1.50 38.1	0.065 1.7	16 ga. round	3500 lbf 15568 N
D 2.00	D 1.69	3/8 x 16	1/2 x 13	5/8 x 11	3/4 x 10	1.94 49.3	0.41 10.4	1.00 25.4	1.90 48.3	0.109 2.8	2.0" Sch 10 pipe	3500 lbf 15568 N
D 2.00	D 1.90	3/8 x 16	1/2 x 13	5/8 x 11	3/4 x 10	1.94 49.3	0.41 10.4	1.00 25.4	2.00 50.8	0.065 1.7	16 ga. round	3500 lbf 15568 N

Specification

- Polyglass filled nylon, black

On request

- Additional inch and metric thread sizes

Information

SN 992 threaded tube ends support more weight than traditional brass insert tube ends, at a fraction of the cost. It's an easy and cost-effective way to attach leveling mounts and glides to the tubes and pipes commonly used to construct frames, conveyor bases and industrial machinery.

Use a plastic mallet or a similar tool, hammer the threaded tube end into the bottom of the tube and attach the mount.

see also...

- *Threaded Tube Ends SN 993 (Square Type, without Insert)* → page 1573
- *Threaded Tube Ends EN 448 (Round Type, with Nickel Plated Brass Insert)* → page 1576
- *Threaded Tube Ends EN 458 (Round Type, with Brass Insert)* → page 1574
- *Threaded Tube Ends GN 992 (Aluminum / Stainless Steel, Round or Square Type)* → page 1581

How to order

SN 992-D¹1.50-D²1.38-3/8X16

- ¹ Outer diameter d₁
- ² Inner diameter d₂
- ³ Thread d₃