



Inch table

Dimensions in: inches - millimeters

¹ S ₁ Outer \square	² S ₂ Inner \square	³ d	l ₁	l ₂	t	External diameter of tube	Wall thickness of tube	Comparable material gauge	Load rating			
V 1.50	V 1.39	3/8 x 16	1/2 x 13	5/8 x 11	3/4 x 10	1.72 43.7	0.33 8.4	1.00 25.4	1.50 38.1	0.065 1.7	16 ga. square	3500 lbf 15568 N
V 1.50	V 1.27	3/8 x 16	1/2 x 13	5/8 x 11	3/4 x 10	1.72 43.7	0.33 8.4	1.00 25.4	1.50 38.1	0.120 3.0	11 ga. square	3500 lbf 15568 N
V 2.00	V 1.90	3/8 x 16	1/2 x 13	5/8 x 11	3/4 x 10	1.72 43.7	0.33 8.4	1.00 25.4	2.00 50.8	0.065 1.7	16 ga. square	3500 lbf 15568 N
V 2.00	V 1.81	3/8 x 16	1/2 x 13	5/8 x 11	3/4 x 10	1.97 50.0	0.41 10.4	1.00 25.4	2.00 50.8	0.120 3.0	11-12 ga. square	3500 lbf 15568 N

Specification

- Polyglass filled nylon, black

On request

- Additional inch and metric thread sizes

Information

SN 993 threaded tube ends support more weight than traditional brass insert tube ends, at a fraction of the cost. It's an easy and cost-effective way to attach leveling mounts and glides to the tubes and pipes commonly used to construct frames, conveyor bases and industrial machinery.

Use a plastic mallet or a similar tool, hammer the threaded tube end into the bottom of the tube and attach the mount.

see also...

- *Threaded Tube Ends SN 992 (Round Type, without Insert) → page 1572*
- *Threaded Tube Ends EN 348 (Square Type, with Nickel Plated Brass Insert) → page 1578*
- *Threaded Tube Ends EN 448 (Square Type, with Nickel Plated Brass Insert) → page 1578*
- *Threaded Tube Ends GN 992 (Aluminum / Stainless Steel, Round or Square Type) → page 1581*

<p>How to order</p> <p>SN 993-V2.00-V1.81-3/4X10</p>	¹	Outer square s ₁
	²	Inner square s ₂
	³	Thread d

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10