



3 Type

- A Without handle
- D With revolving handle

Universal table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Pilot hole	b	d ₃	d ₄	d ₅ Thread	d ₆	l ₁	l ₂ ≈	l ₃ ≈	l ₄	l ₅	r	s
50 1.97	P 4	11 0.43	16 0.63	13 0.51	M 6	13.5 0.53	20 0.79	9 0.35	23 0.91	27 1.06	50 1.97	20 0.79	10 0.39
65 2.56	P 4	13 0.51	20 0.79	13 0.51	M 6	15.5 0.61	24 0.94	10 0.39	28 1.10	27 1.06	55 2.17	26 1.02	13 0.51
80 3.15	P 4	14 0.55	20 0.79	17 0.67	M 6	15.5 0.61	27 1.06	10 0.39	31 1.22	40 1.57	71 2.80	32.5 1.28	15 0.59
100 3.94	P 4	14 0.55	24 0.94	21 0.83	M 8	20 0.79	29 1.14	11 0.43	35 1.38	50 1.97	85 3.35	42 1.65	16 0.63
125 4.92	P 6	16 0.63	32 1.26	23 0.91	M 8	24 0.94	35 1.38	13 0.51	44 1.73	55 2.17	99 3.90	53.5 2.11	18 0.71
150 5.91	P 6	18 0.71	32 1.26	25 0.98	M 10	28 1.10	37 1.46	13 0.51	48 1.89	65 2.56	113 4.45	65 2.56	20 0.79
200 7.87	P 6	21 0.83	40 1.57	28 1.10	M 10	34 1.34	44 1.73	16 0.63	58 2.28	85 3.35	143 5.63	88 3.46	24 0.94
250 9.84	P 6	22 0.87	48 1.89	28 1.10	M 10	40 1.57	49 1.93	17 0.67	66 2.60	85 3.35	151 5.94	110 4.33	30 1.18
300 11.81	P 6	24 0.94	58 2.28	28 1.10	M 10	56.5 2.22	55 2.17	18 0.71	76 2.99	85 3.35	161 6.34	132.5 5.22	35 1.38

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 300 °F (150 °C)
- Black
- Hub bushing
Steel, zinc plated
- Revolving handle
Plastic
Duroplast (Phenolic PF)
- Black, shiny finish
- Threaded spindle
Steel, zinc plated
- Keyways WN / DIN 6885 → page XYZ / XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

Information

VPRA solid disk handwheels with revolving handle are distinguished by their modern design. An excellent choice for light-medium duty applications. No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- Three Spoked Handwheels VRAF-MR → page 263
- Countersunk Washers GN 184 (for Axial Fixing) → page 1150

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

How to order VPRA-50-P4-A	1 Handwheel diameter d ₁
	2 Pilot hole d ₂
	3 Type