


Inch | Metric



2 Bore code

- B** Without keyway
- K** With keyway

4 Type

- A** Without revolving handle
- R** With revolving handle

Specification

Body

- Aluminum die-cast
- Contact face of hub machined
- Rim turned
- Radial and axial runout of the rim < 0.4 mm
- Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Silver, RAL 9006, textured finish **● SR**

Cover

- Plastic, Polyamide (PA)
- Light gray

Stepped cylindrical revolving handle GN 798.2

- Plastic, Polyamide (PA)
- Black, matte finish
- Spindle
 - Steel, zinc plated, blue passivated finish

Mini cylindrical revolving handle GN 599.5

- Plastic, Polyamide (PA)
- Black, matte finish
- Spindle
 - Stainless steel AISI 303

RoHS

Flat-faced solid disk handwheels GN 923 are distinguished by their modern design.

The removable plastic cover shrouds the assembly hardware such as screws and countersunk washers, as well as the shaft end.

No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

	Page
GN 321 Solid Disk Handwheels (Aluminum, Rim Highly Polished)	QVX

Technical Information

Keyways WN 6885 / P9 DIN 6885-1	QVX
Cross Holes GN 110	QVX
ISO Fundamental Tolerances	QVX

Accessory

GN 184 Countersunk Washers	QVX
-----------------------------------	-----

How to order (Inch)

1	Handwheel diameter d_1
2	Bore code
3	Bore diameter d_2
4	Type
5	Color

GN 923-80-B1/2-A-SW

How to order (Metric)

1	Handwheel diameter d_1
2	Bore code
3	Bore diameter d_2
4	Type
5	Color

GN 923-200-B 20 -A-SR

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4



Inch table



Dimensions in: inches / millimeters

d₁	d₂ H7 Bore	d₃	d₄	b	h	l₁	l₂ ≈	l₃ ≈	r	Ø Handle GN 798.2	Recommended countersunk washer
3.15 80	1/2	1.02 26	0.67 17	0.51 13	0.28 7	0.63 16	1.02 26	1.71 43.5	1.08 27.5	0.63 16	184-16
3.94 100	1/2	1.10 28	0.87 22	0.55 14	0.37 9.5	0.67 17	1.18 30	2.28 58	1.42 36	0.71 18	184-20
4.92 125	1/2	1.22 31	0.87 22	0.59 15	0.43 11	0.71 18	1.30 33	2.40 61	1.79 45.5	0.87 22	184-20
5.51 140	5/8	1.42 36	1.12 28.5	0.65 16.5	0.51 13	0.75 19	1.42 36	2.99 76	2.05 52	0.94 24	184-25
6.30 160	5/8	1.42 36	1.12 28.5	0.71 18	0.57 14.5	0.79 20	1.54 39	2.99 76	2.40 61	0.94 24	184-25
7.87 200	3/4	1.65 42	1.42 36	0.81 20.5	0.63 16	0.94 24	1.77 45	3.35 85	3.05 77.5	0.98 25	184-32

Metric table



Dimensions in: millimeters / inches

d₁	d₂ H7 Bore	d₃	d₄	b	h	l₁	l₂ ≈	l₃ ≈	r	Ø Handle GN 798.2	Ø Handle GN 599.5	Recommended countersunk washer	
50 1.97	6	8	20 0.79	13 0.51	13 0.51	7 0.28	16 0.63	26 1.02	20 0.79	16 0.63	-	13 0.51	184-12
63 2.48	8	10	23 0.91	17 0.67	13 0.51	7 0.28	16 0.63	26 1.02	20 0.79	20.5 0.81	-	13 0.51	184-16
80 3.15	10	12	26 1.02	17 0.67	13 0.51	7 0.28	16 0.63	26 1.02	43.5 1.71	27.5 1.08	16 0.63	-	184-16
100 3.94	10	12	28 1.10	22 0.87	14 0.55	9.5 0.37	17 0.67	30 1.18	58 2.28	36 1.42	18 0.71	-	184-20
125 4.92	12	14	31 1.22	22 0.87	15 0.59	11 0.43	18 0.71	33 1.30	61 2.40	45.5 1.79	22 0.87	-	184-20
140 5.51	14	16	36 1.42	28.5 1.12	16.5 0.65	13 0.51	19 0.75	36 1.42	76 2.99	52 2.05	24 0.94	-	184-25
160 6.30	14	16	36 1.42	28.5 1.12	18 0.71	14.5 0.57	20 0.79	39 1.54	76 2.99	61 2.40	24 0.94	-	184-25
200 7.87	18	20	42 1.65	36 1.42	20.5 0.81	16 0.63	24 0.94	45 1.77	85 3.35	77.5 3.05	25 0.98	-	184-32