



**Universal table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> Bore	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	b	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>
60 2.36	Blank	24 0.94	34 1.34	26 1.02	16 0.63	32 1.26	16 0.63	10 0.39	26 1.02	6 0.24
75 2.95	Blank	30 1.18	40 1.57	32 1.26	20 0.79	40 1.57	20 0.79	12 0.47	32.5 1.28	7.5 0.30
90 3.54	Blank	35 1.38	47 1.85	40 1.57	20 0.79	44 1.73	24 0.94	14 0.55	36.7 1.44	7.3 0.29

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 266 °F (130 °C)  
- Black, shiny finish
- Hub bushing  
Steel, zinc plated
- Keyways WN / DIN 6885 → page XYZ / XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

**On request**

- Other modifications such as inch and metric through bores, blind bores, threads, etc.

**Information**

VUA five-lobed control knobs are ideally suited for light-medium duty adjusting or clamping applications.

see also...

- Five-Lobed Control Knobs VU → page 277
- Five-Lobed Control Knobs VUM → page 279

How to order

<sup>1</sup> <sup>2</sup>  
**VUA-75-BLANK**

- 1 Knob diameter d<sub>1</sub>
- 2 Bore