


Inch | Metric



**2 Bore code**

**B** Without keyway

**4 Type**

**A** Without revolving handle  
**R** With revolving handle

**Specification**

**Body**

- Aluminum die-cast
- Contact face of hub machined
- Rim turned
- Radial and axial runout < 0.4 mm
- Powder coated
  - Black, RAL 9005, textured finish
  - Silver, RAL 9006, textured finish

● **SW**  
● **SR**

**Cover**

Plastic, Polyamide (PA)  
Light gray

**Stepped cylindrical revolving handle GN 798.2**

- Plastic, Polyamide (PA)
- Black, matte finish
- Spindle
  - Steel, zinc plated, blue passivated finish

RoHS

Flat-faced spoked handwheels GN 924 are distinguished by their modern design.

The removable plastic cover shrouds the mounting components such as screws, countersunk washers as well as the shaft end.

No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

	Page
<b>GN 322</b> Two Spoked Handwheels (Aluminum, Rim Highly Polished)	QVX

**Technical Information**

Keyways WN 6885 / P9 DIN 6885-1	QVX
Cross Holes GN 110	QVX
ISO Fundamental Tolerances	QVX

**Accessory**

<b>GN 184</b> Countersunk Washers	QVX
-----------------------------------	-----

**How to order (Inch)**

<b>1</b>	Handwheel diameter $d_1$
<b>2</b>	Bore code
<b>3</b>	Bore diameter $d_2$
<b>4</b>	Type
<b>5</b>	Color

**GN924-125-B1/2-A-SR**

**How to order (Metric)**

<b>1</b>	Handwheel diameter $d_1$
<b>2</b>	Bore code
<b>3</b>	Bore diameter $d_2$
<b>4</b>	Type
<b>5</b>	Color

**GN924-200-B18-R-SW**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

## Inch table

1

3

Dimensions in: inches / millimeters

<b>d<sub>1</sub></b>	<b>d<sub>2</sub> H7</b> Bore	<b>d<sub>3</sub></b>	<b>d<sub>4</sub></b>	<b>b</b>	<b>h</b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub> ≈</b>	<b>l<sub>3</sub> ≈</b>	<b>r</b>	<b>Ø</b> Handle GN 798.2	Recommended countersunk washer
4.92 125	1/2	1.22 31	0.91 23	0.59 15	0.43 11	0.71 18	1.32 33.5	2.42 61.5	1.79 45.5	0.87 22	184-20
5.51 140	5/8	1.42 36	1.12 28.5	0.65 16.5	0.51 13	0.75 19	1.44 36.5	3.01 76.5	2.05 52	0.94 24	184-25
6.30 160	5/8	1.42 36	1.12 28.5	0.71 18	0.57 14.5	0.79 20	1.56 39.5	3.01 76.5	2.40 61	0.94 24	184-25
7.87 200	3/4	1.65 42	1.42 36	0.81 20.5	0.63 16	0.94 24	1.79 45.5	3.35 85	3.05 77.5	0.98 25	184-32

## Metric table

1

3

Dimensions in: millimeters / inches

<b>d<sub>1</sub></b>	<b>d<sub>2</sub> H7</b> Bore	<b>d<sub>3</sub></b>	<b>d<sub>4</sub></b>	<b>b</b>	<b>h</b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub> ≈</b>	<b>l<sub>3</sub> ≈</b>	<b>r</b>	<b>Ø</b> Handle GN 798.2	Recommended countersunk washer	
125 4.92	12	14	31 1.22	23 0.91	15 0.59	11 0.43	18 0.71	33.5 1.32	61.5 2.42	45.5 1.79	22 0.87	184-20
140 5.51	14	16	36 1.42	28.5 1.12	16.5 0.65	13 0.51	19 0.75	36.5 1.44	76.5 3.01	52 2.05	24 0.94	184-25
160 6.30	14	16	36 1.42	28.5 1.12	18 0.71	14.5 0.57	20 0.79	39.5 1.56	76.5 3.01	61 2.40	24 0.94	184-25
200 7.87	18	20	42 1.65	36 1.42	20.5 0.81	16 0.63	24 0.94	45.5 1.79	85 3.35	77.5 3.05	25 0.98	184-32