



SS Stainless Steel

Specification

1 4 5

- Lever body
 - Plastic **KT**
 - Nylon thermoplastic
 - Glass fiber reinforced
 - With molded-in stainless steel inlay
 - Temperature resistant up to 230 °F (110 °C)
- Color
 - Black, RAL 9005, textured finish **● SW**
 - Orange, RAL 2004, textured finish **● OS**
 - Gray, RAL 7035, textured finish **● GS**
- Push button
 - Nylon plastic
 - Black, RAL 9005 **● S**
 - Orange, RAL 2004 **● O**
 - Gray, RAL 7035 **● G**
- Insert
 - Stainless steel AISI 303
- ISO Fundamental Tolerances → page 2129
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

Made in the USA, WN 303.1 adjustable levers with push button are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.

All such levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

The push button is a design element and allows for effortless release action. However, this design is limited to applications that do not require the lever to be disassembled.

see also...

- Adjustable Levers WN 303.1 (Nylon Plastic, with Push Button, Threaded Stud Type) → page 450
- Adjustable Levers GN 303.1 (Zinc Die-Cast, with Push Button, Tapped Type) → page 438
- Adjustable Levers WN 300.1 (Nylon Plastic, Tapped or Plain Bore Type) → page 418
- Adjustable Levers GN 300.1 (Zinc Die-Cast, Tapped or Plain Bore Type) → page 406
- Adjustable Levers GN 300.5 (Stainless Steel, Matte Shot-Blasted Finish) → page 430

On request

- Special colors, bores, and threads

How to order (Inch)	1 Material
WN 303.1-KT-30-10X32-SW-O	2 Lever length l_1
	3 Thread d_1 (Bore d_2)
	4 Lever color
	5 Push button color
How to order (Metric)	1 Material
WN 303.1-KT-63-B6-OS-S	2 Lever length l_1
	3 Bore d_2 (Thread d_1)
	4 Lever color
	5 Push button color

Inch table

Dimensions in: inches - *millimeters*

l ₁	d ₁ Thread			d ₂ +0.001 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
1.18 30	10 x 32	10 x 24	1/4 x 20	B 1/4	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.20 30.5	0.14 3.5	0.35 9
1.77 45	10 x 32	10 x 24	1/4 x 20	B 1/4	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5	0.35 9
2.48 63	1/4 x 20	5/16 x 18	-	B 1/4	B 5/16	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4	0.43 11
3.07 78	5/16 x 18	3/8 x 16	3/8 x 24	B 5/16	B 3/8	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55	0.16 4	0.55 14

Metric table

Dimensions in: millimeters - *inches*

l ₁	d ₁ Thread			d ₂ H7 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
30 1.18	M 3	-	-	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14	7 0.28
30 1.18	M 4	M 5	M 6	B 5	B 6	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14	9 0.35
45 1.77	M 4	M 5	M 6	B 6	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14	9 0.35
63 2.48	M 6	M 8	-	B 6	B 8	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	45 1.77	4 0.16	11 0.43
78 3.07	M 8	M 10	-	B 8	B 10	16 0.63	22.2 0.87	36 1.42	8 0.31	55 2.17	4 0.16	14 0.55

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

