



Inch table

Dimensions in: inches - millimeters

1	2	3								
l_1	d_1	l_2				d_3	d_4	h_1	h_2	h_3
1.77 45	10 x 32	0.79 20	1.26 32	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35
1.77 45	10 x 24	0.79 20	1.26 32	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35
1.77 45	1/4 x 20	0.79 20	1.26 32	1.77 45	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35
2.48 63	1/4 x 20	0.98 25	-	-	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45
2.48 63	5/16 x 18	0.79 20	1.26 32	1.57 40	2.48 63	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45
2.48 63	3/8 x 16	0.79 20	1.26 32	2.48 63	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45
3.07 78	3/8 x 16	0.79 20	1.26 32	1.57 40	2.48 63	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55
3.62 92	3/8 x 16	1.26 32	2.48 63	-	-	0.75 19	0.99 25.2	1.69 43	0.43 11	2.56 65
3.62 92	1/2 x 13	1.26 32	1.57 40	2.48 63	-	0.75 19	0.99 25.2	1.69 43	0.43 11	2.56 65

Specification

- Lever body
Nylon thermoplastic
 - Glass fiber reinforced
 - With molded-in stainless steel inlay
 - Temperature resistant up to 230 °F (110 °C)
- Color
 - Black, RAL 9005, textured finish **SW**
 - Orange, RAL 2004, textured finish **OS**
 - Gray, RAL 7035, textured finish **GR**
- Threaded stud / retaining screw
Steel
 - Blackened finish
 - Not removable, loctited
 - Property class 5.8
- Strength Values of Screws → page 2127
- Plastic Characteristics → page 2135
- RoHS compliant



Information

WN 400 fixed clamping levers are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.

The solid steel tapped insert allows the operator the ability to apply additional torque where needed to the item being clamped or fastened.

see also...

- Fixed Clamping Levers WN 400 (Tapped Type) → page 542

On request

- With all stainless steel components
- Special inch and metric bores or threads

How to order	1	Lever length l_1
	2	Thread d_1
	3	Thread length l_2
	4	Color

WN 400-45-10X24-20-SW

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

