



Metric



Metric table

1		2		Dimensions in: millimeters / inches										
b	d ₁ F9			d ₂	l ₁	l ₂	l ₃	l ₄	l ₅	m ₁	m ₂	m ₃	m ₄	
33 1.30	B 8	B 10	B 12	B 14	4.5 0.18	47 1.85	30.5 1.20	9.5 0.37	24.5 0.96	22 0.87	20 0.79	21 0.83	23.5 0.93	20 0.79

Specification

Clamping plate

Zinc die-cast

- Powder coated
- Black, textured finish

Adjustable lever GN 302.1

- Handle
- Zinc die-cast
- Powder coated
- Black, RAL 9005, textured finish
- Insert / Threaded stud
- Stainless steel AISI 303

RoHS

Clamping plates GN 954.7 are used in connection with position indicators digital EN 954 / EN 954.2. The mounting holes support typical bore hole patterns.

In a simpler manner and without great construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with bore diameter 6.1mm to accommodate the torque support of the position indicator.

The clamping plate can be installed so that the adjustable lever is situated as required either on the right or the left.

see also...

	Page
EN 954 Digital Position Indicators (Steel Shaft Receptacle)	QVX
EN 954.2 Digital Position Indicators (Stainless Steel Shaft Receptacle)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

GN954.7-33-B10

- 1 Width b
- 2 Bore d₁

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

