



4 Type
B Pin with snap-on securing collar

Inch table

Dimensions in: inches - millimeters

d ₁ ^{+0.001} Bore	l ₁		d ₂		a	b	d ₃	l ₂		l ₃		l ₄
	Short	Long	Right hand thread	Left hand thread				Short	Long	Short	Long	
B 1/4	0.47 12	0.94 24	1/4 x 28	1/4 x 28L	0.51 13	0.24 6	0.39 10	0.94 24	1.42 36	1.22 31	1.69 43	0.35 9
B 5/16	0.63 16	1.26 32	5/16 x 24	5/16 x 24L	0.63 16	0.31 8	0.55 14	1.26 32	1.89 48	1.65 42	2.28 58	0.47 12
B 3/8	0.79 20	1.57 40	3/8 x 24	3/8 x 24L	0.75 19	0.39 10	0.71 18	1.57 40	2.36 60	2.05 52	2.83 72	0.59 15
B 1/2	1.10 28	2.20 56	1/2 x 20	1/2 x 20L	0.98 25	0.51 13	0.94 24	2.20 56	3.31 84	2.83 72	3.98 101	0.91 23
B 5/8	1.26 32	-	5/8 x 18	5/8 x 18L	1.26 32	0.63 16	1.02 26	2.52 64	-	3.27 83	-	0.94 24

Specification

- Fork body / pin
Steel **ST**
- Property class 5
- Zinc plated, blue passivated finish
- Snap-on securing collar
Steel, zinc plated, blue passivated finish
- RoHS compliant

On request

- Additional sizes

Information

WN 751 clevis fork joints are mainly used with pneumatic or hydraulic cylinders. They consist of a clevis fork head according to WN 71752 and a pin with snap-on securing collar.

see also...

- Types of Clevis Fork Joint Pins → page 1745
- Clevis Fork Joints WN 751 (Inch Size, Stainless Steel) → page 1749
- Clevis Fork Joints GN 751 (Metric Size, Steel) → page 1744
- Clevis Fork Joints GN 751 (Metric Size, Stainless Steel) → page 1746
- Clevis Fork Joints GN 751 (Metric Size, Aluminum) → page 1747

How to order (Clevis fork joint)	1 Bore d ₁
	2 Length l ₁
	3 Thread d ₂
	4 Type
	5 Material
WN 751-B5/16-16-5/16X24-B-ST	
How to order (Clevis fork head)	1 Bore d ₁
	2 Length l ₁
	3 Thread d ₂
	5 Material
WN 71752-B1/4-12-1/4X28-ST	