



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂	Length l										d ₃	h ₁	h ₂
		ZP												
22 0.87	M 4	10 0.39	25 0.98	-	-	-	-	-	-	-	-	15 0.59	14 0.55	6 0.24
22 0.87	M 5	10 0.39	15 0.59	-	-	-	-	-	10 0.39	-	-	15 0.59	14 0.55	6 0.24
22 0.87	M 6	10 0.39	15 0.59	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	-	-	-	15 0.59	14 0.55	6 0.24
24 0.94	M 4	10 0.39	25 0.98	-	-	-	-	-	-	-	-	15 0.59	14 0.55	6 0.24
24 0.94	M 5	10 0.39	-	-	-	-	-	-	-	-	-	15 0.59	14 0.55	6 0.24
24 0.94	M 6	10 0.39	15 0.59	25 0.98	-	-	-	-	-	-	-	15 0.59	14 0.55	6 0.24
26 1.02	M 5	10 0.39	15 0.59	25 0.98	-	-	-	-	-	-	-	16 0.63	15 0.59	6 0.24
26 1.02	M 6	10 0.39	15 0.59	20 0.79	25 0.98	40 1.57	-	-	20 0.79	30 1.18	-	16 0.63	15 0.59	6 0.24
26 1.02	M 8	25 0.98	-	-	-	-	-	-	-	-	-	16 0.63	15 0.59	6 0.24

Specification

- Body
Nylon plastic
- Glass filled
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish

- **ZP**
Threaded stud
Steel, zinc plated

- **ZPX**
Threaded stud
Stainless steel AISI 304

- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

On request

- For certain minimum quantities, custom colors or special studs

Information

More shock proof than their phenolic counterpart, these ZP and ZPX knurled screws provide excellent slip-free clamping and fastening.

How to order (Steel threaded stud)	1 Handle diameter d ₁
ZP-24-M5-10	2 Thread d ₂
	3 Length l

How to order (Stainless steel threaded stud)	1 Handle diameter d ₁
ZPX-26-M6-20	2 Thread d ₂
	3 Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4