



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

1			2					
l_1			d_1	d_2	d_3	h_1	$h_2 \approx$	$l_2 \approx$
GN 99.5	GN 99.6 AISI 304	GN 99.6 AISI 316L						
63 2.48	63 2.48	63 2.48	M 8	16 0.63	10 0.39	12.5 0.49	30.5 1.20	60 2.36
80 3.15	80 3.15	80 3.15	M 10	20 0.79	12 0.47	15 0.59	37 1.46	76 2.99
100 3.94	100 3.94	100 3.94	M 12	25 0.98	14 0.55	19 0.75	46 1.81	95 3.74
125 4.92	125 4.92	-	M 16	32 1.26	18 0.71	25 0.98	58.5 2.30	119 4.69
160 6.30	160 6.30	-	M 20	40 1.57	20 0.79	31 1.22	73 2.87	152 5.98

Specification

- GN 99.5**
Steel, zinc plated, blue passivated finish —
- GN 99.6**
Stainless steel, matte shot-blasted finish
- AISI 304 —
- AISI 316L **A4**
- Clamp arm
Butt-welded to tapped hub
- [Stainless Steel Characteristics](#) → page 2143
- RoHS compliant

Information

Latest production techniques make these GN 99.5 and GN 99.6 clamp nuts an extremely good value.

see also...

- Clamping Levers DIN 99 (Steel, Blackened Finish) → page 540
- Clamping Levers DIN 99 (Stainless Steel, Matte Shot-Blasted Finish) → page 540
- Clamp Nuts GN 206 (Malleable Iron) → www.jwwinco.com
- Clamp Nuts GN 206 (Stainless Steel) → www.jwwinco.com

On request

- Special inch and metric bores or threads

How to order (Steel) GN 99.5-100-M12	1 Lever length l_1
	2 Thread d_1
How to order (Stainless steel AISI 304) GN 99.6-80-M10	1 Lever length l_1
	2 Thread d_1
How to order (Stainless steel AISI 316L) GN 99.6-80-M10-A4	1 Lever length l_1
	2 Thread d_1
	3 Material