


Metric



Metric table

Dimensions in: millimeters / inches

d <sub>1</sub>	d <sub>2</sub>		d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> min.	l <sub>3</sub> ±0.5
13 0.51	M 5	M 6	11 0.43	27 1.06	14 0.55	2 0.08
17 0.67	M 6	-	11 0.43	40 1.57	20 0.79	2 0.08
17 0.67	M 8	-	11 0.43	40 1.57	25 0.98	7 0.28
21 0.83	M 6	M 8	17 0.67	50 1.97	25 0.98	4 0.16
21 0.83	M 10	-	17 0.67	50 1.97	25 0.98	3 0.12
23 0.91	M 8	-	18 0.71	55 2.17	25 0.98	4 0.16
23 0.91	M 10	-	18 0.71	55 2.17	25 0.98	3 0.12
25 0.98	M 8	-	19 0.75	65 2.56	30 1.18	3 0.12
25 0.98	M 10	M 12	19 0.75	65 2.56	30 1.18	4 0.16
28 1.10	M 8	-	21 0.83	85 3.35	40 1.57	6 0.24
28 1.10	M 10	-	21 0.83	85 3.35	40 1.57	3 0.12
28 1.10	M 12	-	21 0.83	85 3.35	40 1.57	5 0.20
28 1.10	M 14	-	21 0.83	85 3.35	40 1.57	5 0.20
29 1.14	M 8	-	22 0.87	112 4.41	40 1.57	2 0.08
29 1.14	M 12	-	22 0.87	112 4.41	40 1.57	8 0.31

Specification

Plastic, Phenolic (PF)

• Operating temperature up to 266 °F (130 °C)

• Black, shiny finish

• Molded-in thread

RoHS

Cylindrical handles MC are mainly used on threaded shafts such as gear lever arms or as fixed grip handles. Make sure that the threaded end of the shaft is long enough and seats flush inside the threaded hole of the handle, otherwise the plastic may break under excessive stress.

Technical Information

Plastic Characteristics

Page

QVX

How to order

**MC-28-M10**

1 Handle diameter d<sub>1</sub>

2 Thread d<sub>2</sub>