



3 Type
A Without handle
D With revolving handle

Universal table

1 d ₁	2 d ₂ Pilot Hole	d ₃	d ₄	d ₆	s	l ₁	l ₂	l ₃	l ₄	l ₅	b	d ₅
100 3.94	P 4	24 0.94	21 0.83	18 0.71	15 0.59	24 0.94	12 0.47	46 1.81	50 1.97	96 3.78	20 0.79	M 6
125 4.92	P 6	24 0.94	21 0.83	20 0.79	17 0.67	28 1.10	12 0.47	51 2.01	50 1.97	101 3.98	24 0.94	M 6
160 6.30	P 6	32 1.26	23 0.91	30 1.18	20 0.79	31 1.22	15 0.59	61 2.40	70 2.76	131 5.16	28 1.10	M 8
200 7.87	P 6	40 1.57	26 1.02	35 1.38	24 0.94	40 1.57	15 0.59	74 2.91	90 3.54	164 6.46	32 1.26	M 10

Dimensions in: millimeters - inches

Specification

- Nylon plastic
 - Glass filled
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
- Hub bushing
 - Steel, zinc plated
- Revolving handle
 - Nylon plastic
 - Black fiber reinforced
 - Threaded spindle
 - Steel, zinc plated
- Keyways WN / DIN 6885 → page XYZ / XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

Information

SHA glass filled nylon plastic handwheels with revolving handle are of modern design. They are an excellent choice for light to medium duty applications. No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- Countersunk Washers GN 184 (for Axial Fixing) → page 1150
- Solid Disk Handwheels SHA-MRP → page 250

How to order

SHA-160-P6-D

- 1** Handwheel diameter d₁
- 2** Pilot hole d₂
- 3** Type