



- 3 Type**
- A Without handle
 - D With revolving handle

Universal table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Pilot hole	d ₃	d ₄	b	l ₁	l ₂	l ₃	l ₄	l ₅	d ₅
100 3.94	P 4	24 0.94	17 0.67	15 0.59	33 1.30	11 0.43	40 1.57	45 1.77	85 3.35	M 8
125 4.92	P 6	24 0.94	23 0.91	17 0.67	36 1.42	13 0.51	46 1.81	61 2.40	107 4.21	M 8
150 5.91	P 6	32 1.26	25 0.98	20 0.79	37 1.46	13 0.51	49 1.93	71 2.80	120 4.72	M 10
175 6.89	P 6	40 1.57	25 0.98	22 0.87	41 1.61	16 0.63	56 2.20	71 2.80	127 5.00	M 10
200 7.87	P 6	40 1.57	28 1.10	24 0.94	44 1.73	16 0.63	61 2.40	92 3.62	153 6.02	M 10
250 9.84	P 6	48 1.89	28 1.10	28 1.10	49 1.93	17 0.67	72 2.83	92 3.62	164 6.46	M 10
300 11.81	P 6	58 2.28	28 1.10	34 1.34	54 2.13	18 0.71	78 3.07	92 3.62	170 6.69	M 10

Specification

- Plastic
Duroplast (Phenolic PF)
- Fiber reinforced
- Temperature resistant up to 300 °F (150 °C)
- Black, shiny finish
- Hub bushing
Steel, zinc plated
- Revolving handle
Plastic
Duroplast (Phenolic PF)
- Black, shiny finish
- Rim
Steel, zinc plated
- Keyways WN / DIN 6885 → page XYZ / XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

Information

VRAF three spoked handwheels are distinguished by modern design. An excellent choice for light-medium duty applications.

No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- Three Spoked Handwheels VRAF-MR → page 263
- Countersunk Washers GN 184 (for Axial Fixing) → page 1150

How to order 1 2 3 VRAF-100-P4-A	1 Handwheel diameter d ₁
	2 Pilot hole d ₂
	3 Type

1.1 1.2 1.3 1.4 2.1 2.2 2.3 2.4