



Universal table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Pilot hole	d ₃	d ₄	d ₅	b	l ₁	l ₂	l ₃	l ₄	l ₅
75 2.95	P 4	24 0.94	34 1.34	17 0.67	20 0.79	39 1.54	19 0.75	11 0.43	22 0.87	43 1.69
90 3.54	P 6	32 1.26	44 1.73	17 0.67	20 0.79	42 1.65	22 0.87	12 0.47	25 0.98	43 1.69

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 266 °F (130 °C)
- Black, shiny finish
- Hub bushing
Steel, zinc plated
- Revolving handles
Plastic
Duroplast (Phenolic PF)
- Black, shiny finish
- Threaded spindle
Steel, zinc plated
- Keyways WN / DIN 6885 → page XYZ / XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Other modifications such as inch and metric blind bores, threads, etc.

Information

VUM five-lobed control knobs with revolving handle are ideally suited for light-medium duty adjusting or clamping applications.

see also...

- Five-Lobed Control Knobs VUA → page 278
- Five-Lobed Control Knobs VU → page 277

How to order

¹ ²
VUM-75-P4

- 1 Knob diameter d₁
- 2 Pilot hole d₂

