



Inch table

Dimensions in: inches - millimeters

² l ₁	³ d ₁			d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
1.77 45	10 x 32 10 x 24 1/4 x 20			0.39 10	0.57 14.5	0.96 24.5	0.16 4	0.87 22	0.14 3.5	0.35 9
2.48 63	1/4 x 20 5/16 x 18	-		0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.12 28.5	0.16 4	0.43 11
3.07 78	5/16 x 18 3/8 x 16	-		0.63 16	0.87 22.2	1.42 36	0.31 8	1.34 34	0.16 4	0.55 14

Metric table

Dimensions in: millimeters - inches

² l ₁	³ d ₁			d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
30 1.18	M 4 M 5 M 6			10 0.39	14.5 0.57	24.5 0.96	4 0.16	22 0.87	3.5 0.14	9 0.35
45 1.77	M 4 M 5 M 6			10 0.39	14.5 0.57	24.5 0.96	4 0.16	22 0.87	3.5 0.14	9 0.35
63 2.48	M 6 M 8	-		13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	28.5 1.12	4 0.16	11 0.43
78 3.07	M 8 M 10	-		16 0.63	22.2 0.87	36 1.42	8 0.31	34 1.34	4 0.16	14 0.55

Specification

- Lever body
Plastic **KT**
Nylon thermoplastic
- Glass fiber reinforced
- With molded-in stainless steel inlay
- Temperature resistant up to 230 °F (110 °C)
- Color
Black, RAL 9005, textured finish **● SW**
Orange, RAL 2004, textured finish **● OS**
- Insert / retaining screw
Steel, zinc plated, blue passivated finish
- Plastic Characteristics → page QVX
- ISO Fundamental Tolerances → page QVX
- RoHS compliant

Information

Made in the USA, WN 302.2 adjustable levers have a straight lever parallel to the clamping surface. For some applications this presents an advantage due to limits of space or for visual reasons.

These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

How to order (Inch)		1	Material
¹	²	³	⁴
WN 302.2-KT-63-1/4X20-SW			
2	Lever length l ₁		
3	Thread d ₁		
4	Lever color		

How to order (Metric)		1	Material
¹	²	³	⁴
WN 302-KT-45-M4-OS			
2	Lever length l ₁		
3	Thread d ₁		
4	Lever color		