


Application example



SS Stainless Steel

**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub> min.
1.57 40	1/4 x 20	0.71 18	0.26 6.5	1.02 26	0.43 11
1.57 40	5/16 x 18	0.71 18	0.31 8	1.02 26	0.43 11
1.97 50	5/16 x 18	0.83 21	0.31 8	1.14 29	0.47 12
1.97 50	3/8 x 16	0.83 21	0.39 10	1.14 29	0.47 12
2.36 60	3/8 x 16	0.98 25	0.39 10	1.30 33	0.47 12
2.36 60	1/2 x 13	0.98 25	0.51 13	1.30 33	0.47 12

**Specification**

- Stainless steel AISI 303 **NI**  
Matte shot-blasted finish
- Cross Holes GN 110 → page 2042
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**On request**

- Metric sizes

**Information**

WN 5335.5 quick release star knobs are manufactured from solid stainless steel bar.

They are used in such applications where the knob has to be completely removed after the releasing operation and mounted again rapidly for re-clamping.

The knob is tilted over the threaded spindle. When in position, the knob is brought into a straight position for mating of the two threads on the insert and spindle. The knob will then have to be turned only by a fraction of a rotation to achieve clamping.

see also...

- Star Knobs GN 5335 (with Tapped or Plain Bore, or Blank Type) → page 620

How to order

<sup>1</sup> <sup>2</sup> <sup>3</sup>  
**WN 5335.5-60-3/8X16-NI**

- <sup>1</sup> Handle diameter d<sub>1</sub>
- <sup>2</sup> Thread d<sub>2</sub>
- <sup>3</sup> Material