



SS Stainless Steel

3 Type

A Without thread locking patch

Inch table

Dimensions in: inches - millimeters

1 d ₁	2 d ₂	d ₃	l ₁	l ₂	l ₃	Spring load ≈	
						Initial	End
0.156 4.0	1/4 x 20	0.97 24.6	0.64 16.3	0.17 4.3	0.31 7.9	0.50 lbf 2.22 N	2.00 lbf 8.90 N
0.250 6.4	3/8 x 16	0.97 24.6	0.83 21.1	0.27 6.9	0.44 11.2	0.75 lbf 3.34 N	3.00 lbf 13.34 N
0.312 7.9	1/2 x 13	1.00 25.4	1.08 27.4	0.34 8.6	0.56 14.2	1.00 lbf 4.45 N	4.00 lbf 17.79 N
0.375 9.5	5/8 x 11	1.34 34.0	1.35 34.3	0.42 10.7	0.69 17.5	1.12 lbf 5.00 N	5.00 lbf 22.24 N

Specification

- Threaded body
12L14 steel, zinc plated **ST**
- Plunger pin
Steel, zinc plated
- Pull ring
Stainless steel AISI 301
- Threaded body / plunger pin / pull ring
Stainless steel AISI 303 **NI**
- *Stainless Steel Characteristics* → page 2143
- *RoHS compliant*

On request

- Thread locking patch

Information

WN 717.10 stubby hand retractable spring plungers are ideal for indexing / locating pin applications with limited space.

see also...

- *List of Indexing Plunger Types* → page 915

How to order	1 Pin diameter d ₁
1 2 3 4 WN717.10-0.312-1/2X13-A-ST	2 Thread d ₂
	3 Type
	4 Material